

Eaton BRP30B200R

Catalog Number: BRP30B200R

Eaton BR main breaker loadcenter, Plug-on, 200A,X6,Aluminum, Cover included,NEMA 3R, Metallic, 10 kAIC, BR, 60 circuits, Single pole,30 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers,120/240V



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B200R
UPC	Product Length/Depth
786689059347	34.12 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
22 lb	10 year

Certifications

UL 67

UL 50

Product specifications

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30B200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)