

Eaton BRP30B200RV25

Catalog Number: BRP30B200RV25

BR plug-on neutral loadcenter value pack, 200A, main breaker, 30 spaces, NEMA 3R w/ (2) BR120 & (1) BR230



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B200RV25
UPC	Product Length/Depth
786689058432	34.12 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
26 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Special features

Value pack

Type

Main circuit breaker

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Wire size

#4-1/0 AWG Cu/Al

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP30B200RV25

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

25 kAIC

Number of wires

3

NEMA rating

NEMA 3R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)