

Eaton BRP30L200R

Catalog Number: BRP30L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X5, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 60 Circuits, Single-pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP30L200R
UPC	Product Length/Depth
786689059354	3.88 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
19 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

MLO

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30L200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP30L200R

Catalog Number: BRP30L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X5, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 60 Circuits, Single-pole, 30 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #1–300 kcmil



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP30L200R
UPC	Product Length/Depth
786689059354	3.88 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
19 lb	10 year
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

MLO

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30L200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia