

Eaton BRP40N200

Catalog Number: BRP40N200

Eaton BR convertible loadcenter, Ground bar, includes BREQS125 hold-down screw, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200
UPC	Product Length/Depth
786689044077	39 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP40N200

Catalog Number: BRP40N200

Eaton BR convertible loadcenter, Ground bar, includes BREQS125 hold-down screw, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, Combination, 80 Circuits, Single-pole, 40 Spaces, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP40N200
UPC	Product Length/Depth
786689044077	39 in
Product Height	Product Width
3.88 in	14.13 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 67	
UL 50	

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

80

Number Of Poles

Single-pole

Number of spaces

40

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP40N200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)