

Eaton BRP42BC225

Catalog Number: BRP42BC225

Plug-on neutral main circuit breaker
loadcenter,225A,X8,Copper,Cover included,NEMA
1,Metallic,25kAIC,CSR2225,84 circuits,Single pole,42 spaces,Two
hots, a neutral and a ground,Single-phase,#6-1/0 AWG
Cu/Al,25,Kilo Ampere,25kAIC,Gray,Combina



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP42BC225
UPC	Product Length/Depth
786689055035	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
39.5 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Main circuit breaker

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

225 A

Bus material

Copper

Cover

Cover included

Main circuit breaker

CSR2225

Number of circuits

84

Number Of Poles

Single-pole

Number of spaces

42

Phase

Single-phase

Wire size

#6-1/0 AWG Cu/Al

Accessories

copper bus

Bus Rating

25 kA

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP42BC225](#)

Box size

X8

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Circuit breaker rating

25 kAIC

NEMA rating

NEMA 1

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia