

# Eaton BRP42LC225G

Catalog Number: BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, Main lug only, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, Single-pole, 42 Spaces, a neutral and a ground, Single-phase, 1, 120/240V, #6-1/0 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP42LC225G
<b>UPC</b>	<b>Product Length/Depth</b>
786689055059	39 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
36.3 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Special features

Main Lug Only

### Type

Main Lug Only

### Amperage Rating

225 A

### Bus material

Copper

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Surface, flush

### Number of circuits

84

### Number Of Poles

Single-pole

### Number of spaces

42

### Phase

Single-phase

### Used with

BR

### Voltage rating

120/240V

### Wire size

#6-1/0 AWG Cu/Al

### Box size

X8

### Color

Gray

### Enclosure

NEMA 1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP42LC225G](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP42LC225G

Catalog Number: BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, Main lug only, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, Single-pole, 42 Spaces, a neutral and a ground, Single-phase, 1, 120/240V, #6-1/0 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	BRP42LC225G
<b>UPC</b>	<b>Product Length/Depth</b>
786689055059	39 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
36.3 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Special features

Main Lug Only

### Type

Main Lug Only

### Amperage Rating

225 A

### Bus material

Copper

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Surface, flush

### Number of circuits

84

### Number Of Poles

Single-pole

### Number of spaces

42

### Phase

Single-phase

### Used with

BR

### Voltage rating

120/240V

### Wire size

#6-1/0 AWG Cu/Al

### Box size

X8

### Color

Gray

### Enclosure

NEMA 1

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRP42LC225G](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Quantity

1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)