

# Eaton BRP60B200R

Catalog Number: BRP60B200R

Plug-on neutral main circuit breaker loadcenter, 200A, X10, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 120 circuits, Single pole, 60 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V




Photo is representative

## General specifications

|                                  |                             |
|----------------------------------|-----------------------------|
| <b>Product Name</b>              | <b>Catalog Number</b>       |
| Eaton BR main breaker loadcenter | BRP60B200R                  |
| <b>UPC</b>                       | <b>Product Length/Depth</b> |
| 786689059088                     | 48.75 in                    |
| <b>Product Height</b>            | <b>Product Width</b>        |
| 5.5 in                           | 14.31 in                    |
| <b>Product Weight</b>            | <b>Warranty</b>             |
| 35 lb                            | 10 year                     |
| <b>Certifications</b>            |                             |
| UL 67                            |                             |
| UL 50                            |                             |

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

120

### Number Of Poles

Single-pole

### Number of spaces

60

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X10

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP60B200R](#)

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)