



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BRSUR3040N200**

**UPC:**782116417124

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Factory integrated surge
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BRSUR3040N200](#)

### Certifications:

- UL 67
- UL 50

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## BR style 1-inch loadcenter

**BRSUR3040N200**

**UPC:**782116417124

### Dimensions:

- **Height:** 39 IN
- **Length:** 3.88 IN
- **Width:** 14.31 IN

### Warranties:

- 10 year

### Specifications:

- **Special Features:** Factory integrated surge
- **Type:** Convertible main
- **Amperage Rating:** 200A
- **Box Size:** L1
- **Bus Material:** Aluminum
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** BWH
- **Mounting:** Combination
- **Number Of Circuits:** 40
- **Number Of Spaces:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Voltage Rating:** 120/240V

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BRSUR3040N200](#)

### Certifications:

- UL 67
- UL 50

**Product compliance:** No Data



