

Specifications



Eaton BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V

General specifications

| | |
|-----------------------------|---------------------------|
| PRODUCT NAME | Eaton BR surge loadcenter |
| CATALOG NUMBER | BRSUR4040B200 |
| UPC | 782116417148 |
| PRODUCT LENGTH/DEPTH | 3.88 in |
| PRODUCT HEIGHT | 45 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 45 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |



Powering Business Worldwide

Product specifications

| | |
|-----------------------------|--------------------------|
| SPECIAL FEATURES | Factory integrated surge |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 200 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BWH |
| MOUNTING | Combination |
| NUMBER OF CIRCUITS | 40 |
| NUMBER OF SPACES | 40 |
| PHASE | Single-phase |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | L2 |
| ENCLOSURE | NEMA 1 |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 25 kAIC |
| NUMBER OF WIRES | 3 |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BRSUR4040B200 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton BRSUR4040B200

Eaton BR surge loadcenter, Factory integrated surge, Main circuit breaker, 200 A, L2, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 40/40 Circuits, 40 Spaces, Three-wire, Single-phase, 120/240 V

General specifications

| | |
|-----------------------------|---------------------------|
| PRODUCT NAME | Eaton BR surge loadcenter |
| CATALOG NUMBER | BRSUR4040B200 |
| UPC | 782116417148 |
| PRODUCT LENGTH/DEPTH | 3.88 in |
| PRODUCT HEIGHT | 45 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 45 lb |
| WARRANTY | 10 year |
| CERTIFICATIONS | UL 67 UL 50 |



Powering Business Worldwide

Product specifications

| | |
|-----------------------------|--------------------------|
| SPECIAL FEATURES | Factory integrated surge |
| TYPE | Main circuit breaker |
| AMPERAGE RATING | 200 A |
| BUS MATERIAL | Aluminum |
| COVER | Cover included |
| MAIN CIRCUIT BREAKER | BWH |
| MOUNTING | Combination |
| NUMBER OF CIRCUITS | 40 |
| NUMBER OF SPACES | 40 |
| PHASE | Single-phase |
| VOLTAGE RATING | 120/240 V |
| BOX SIZE | L2 |
| ENCLOSURE | NEMA 1 |
| ENCLOSURE MATERIAL | Metallic |
| INTERRUPT RATING | 25 kAIC |
| NUMBER OF WIRES | 3 |

Resources

| | |
|--------------------------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - BRSUR4040B200 |
| WARRANTY GUIDES | Eaton type BR circuit breaker limited warranty June 2024 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

