

Eaton BSPMA1120S2GR

Catalog Number: BSPMA1120S2GR

Eaton Bussmann series BSPM series surge arrester, Technology type MOV, Surge arrester, Thermoplastic, UL94V12, 50/60 Hz, 200 Kilo Ampere, Thermoplastic, Remote Contact



General specifications

Product Name

Eaton Bussmann series BSPM series surge arrester

Catalog Number

BSPMA1120S2GR

UPC

051712709026

Product Length/Depth

0.71 in

Product Height

3.54 in

Product Width

2.56 in

Product Weight

0.26 lb

Warranty

Five year limited warranty

Compliances

RoHS Compliant

Contact factory

Certifications

UL 94V0

UL Listed



Powering Business Worldwide

Product specifications

Special features

Technology type MOV

Material

Thermoplastic

Enclosure

Thermoplastic, UL94V12

Surge current

200 kA

Mounting Method

35 mm DIN rail

Nominal Discharge Current

20 kA

Short-circuit rating

200 kA

Type

Surge arrestor

Operating voltage

600/1200

Indicator type

Remote contact

Frequency rating

50/60 Hz

Operating temperature

-35 to 85 °C

Application

Surge Protection

Degree of protection

IP20

Resources

Catalogs

BSPMA1120S2GR-120V Single Phase, 1P

Bussmann series complete full line catalog no. 1007

Specifications and datasheets

Eaton Specification Sheet - BSPMA1120S2GR



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)