



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BT7 2-1/2" BT MGL Conduit Body

Crouse-Hinds

Catalog Number	BT7
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet B Mogul Conduit Body, Feraloy Iron Alloy, T Shape, 2-1/2"
Weight per unit	14.7 (lbs/each)
Product Category	Bodies & Covers

Features

dimensions	18.3800 IN X 3.6300 IN X 5.5900 IN
------------	------------------------------------

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Height	3-5/8
Hub Size	2-1/2 in
Length	18-3/8
Width	5-19/32

Descriptions

Description	2-1/2" BT MGL CONDUIT BODY
extra long description	CRS-H BT7 2 1/2 NPT IRON T MOGUL
Features	Crouse-Hinds series mogul bodies are installed in conduit systems to act as pull outlets for conductors that are stiff due to large size or type of insulation. Mogul bodies provide longer openings needed when pulling large conductors and prevent sharp bends and kinks during installation. Mogul conduit bodies are manufactured in trade sizes 1/2" to 6" and are available in Feraloy iron alloy and copper-free aluminum. Our iron alloy bodies are available with a hot dip galvanized finish for added corrosion
Long Description	Eaton Crouse-Hinds series Condulet B mogul conduit body, Feraloy iron alloy, T shape, 2-1/2"
Product Type	2 1/2 NPT Iron T Mogul

Manufacturer Information

Brand	Eaton
GTIN	00782274108001
UPC	782274108001

Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Mogul conduit body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	14.6999

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D