

Eaton BXM-1214

Catalog Number: BXM-1214

Eaton B-Line series cable support fasteners, Conduit and cable, Flange, 0.062lbs, Flexible conduit/cable fasteners, .13" Min, .25" Max mount size, .444" Min, 0.56" Max cable diameter, M8 rod size, Accepts 10/3, romex w ground, Zinc plated

General specifications



Product Name	Catalog Number
Eaton B-Line series conduit cable fastener and support	BXM-1214
	UPC
	781011199838
Product Length/Depth	Product Height
1 in	1 in
Product Width	Product Weight
1 in	0.012 lb
Certifications	
CE	
UL Listed	

Application

Application

Secures cable along flanges

Model

Product Category

Conduit and cable

Type

Flexible conduit/cable fasteners

Mounting method

Flange

Special features

Accepts 10/3, romex with ground

Specifications

Cable diameter - min

0.444 in

Cable diameter - max

0.56 in

Mounting dimensions - min

0.13

Mounting dimensions - max

0.25

Resources

Specifications and datasheets

[Eaton Specification Sheet - BXM-1214](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)