

Eaton C0050E5E

Catalog Number: C0050E5E

Eaton Type MTE industrial control transformer, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°c, 50 va , pv: 200/220/440v, 208/230/460 v



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0050E5E
	UPC
	786680420306
Product Length/Depth	Product Height
3.86 in	3.26 in
Product Width	Product Weight
3 in	4.3 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	CSA Certified
	cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

200/220/440 V, 208/230/460 V, 240/480 V

Temperature rating

55°C

Volt ampere rating

50 VA

Secondary voltage

23/110 V, 24/115 V, 25/120 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0050E5E](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)