



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C0100E5E 100 Va Type Mte Control Transformer

Eaton Corp

Catalog Number	C0100E5E
Manufacturer	Eaton Corp
Description	Eaton Type Mte Industrial Control Transformer, PV: 200/220/440V, 208/230/460V, 240/480V, Taps: None, SV: 23/110V, 24/115V, 25/120V, 55°C, 100 Va
Weight per unit	5.9 (lbs/each)
Product Category	Encapsulated Industrial Contro

Features

dimensions	3.7500 IN X 3.5800 IN X 3.6200 IN
kva rating	100 VA
Primary Voltage	200/220/440 V, 208/230/460 V, 240/480 V
Secondary Voltage	23/110 V, 24/115 V, 25/120 V
Tap Size	NONE

Descriptions

Description	100 VA TYPE MTE CONTROL TRANSFORMER
extra long description	ETN C0100E5E 100 VA Type MTE Contro
Features	Eaton offers a complete line of Type AP, MTE and MTK Industrial Control Transformers, which provide stepped-down voltages to machine tool control devices. Each unit must pass rigid tests for turns ratio, insulation, continuity, and over potential. Performance meets or exceeds ANSI/NEMA ST-1 requirements. With a 50-60 Hz operation standard, transformers are designed for loads requiring extremely good regulation. Regulation also exceeds ANSI/NEMA requirements.
Long Description	Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 100 va
Product Type	100 Va Type Mte Control Transformer

Manufacturer Information

Brand	Eaton
GTIN	00786680420344
Manufacturers Part Number	C0100E5E
UPC	786680420344

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Industrial Control Transformer



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	5.9

Uses, Certifications, and Standards

Application	Other
standard	cUL Certified,UL Listed,CSA Certified,RoHS Compliant
Temperature Rating	55°C