



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C16N 16-14AWG Closed End Wire Nyl Conn W/CRMP SLV

Nsi Industries

| | |
|------------------|---|
| Catalog Number | C16N |
| Manufacturer | Nsi Industries |
| Description | The Easy-Twist C16-N 100-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 22-14 Awg Size Range. Theyâ€™re UL-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need T |
| Weight per unit | 0.1520 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|--------------|
| insulation | Nylon 6-6 |
| Material | Nylon |
| Poles | 1 |
| Voltage Rating | 300 |
| Warranty | 1 YEAR |
| Wire Size | 22-14 AWG |
| Wire Type | CU Wire Only |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | NYLON |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 16-14AWG CLOSED END WIRE NYL CONN W/CRMP SLV |
| extra long description | NSI C16-N CU CMP Splice Long 350 MC |
| Features | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn |
| Long Description | The Easy-Twist C16-N 100-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 22-14 AWG size range. Theyâ€™re UL-certified as self-extinguishing and rated for a maximum temperature of 105Ëš Celsius (221Ëš Fahrenheit). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need t |
| Product Type | Cu CMP Splice Long 350 MCM |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381068019 |
| Manufacturers Part Number | C16-N |
| sub brand | Easy Twist |
| UPC | 662381068019 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------|
| Category Description | TERMINALS |
|----------------------|-----------|

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 100 |
| Weight Per each | 0.152 |

Uses, Certifications, and Standards

| | |
|--------------------------|-------|
| environmental conditions | 105 C |
| Temperature Rating | 105 C |