

Eaton C25BNB220T

Catalog Number: C25BNB220T

Eaton definite purpose contactor, Quick, 20A, 277 Vac, 60 Hz, Open with metal mounting plate, Compact, two-pole, 20A, Contactor, Two-pole, Power terminals: Binding head screw and quick con, Non-reversing

General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25BNB220T
UPC	Product Length/Depth
786685115986	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
.6 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified



Product specifications

Frame size

Compact, two-pole

Type

Non-reversing

Inductive full load

20 A

Model

Contactors

Connection

Quick

Enclosure

Open with metal mounting plate

Terminals

Binding head screw and quick connect terminals (side-by-side)

Amperage Rating

20A

Resistive load

30 A

Number Of Poles

Two-pole

Coil

24 Vac, 50/60 Hz

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

C25BNB 3D Model Xchange

C25BNB 3D Inventor

C25BNB 2D PDF

C25BNB AutoCAD 2D Footprint

C25BNB AutoCAD 2D Footprint (mm)

C25BNB 2D Drawing Xchange

Specifications and datasheets

Eaton Specification Sheet - C25BNB220T

Quick Selector - Definite Purpose Contactors



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia