

Eaton C25BNB230H

Catalog Number: C25BNB230H

Eaton definite purpose contactor, Quick, 30A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25BNB230H
UPC	Product Length/Depth
786685116051	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Two-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

Compact, two-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Binding head screw and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25BNB 3D Inventor](#)

[C25BNB 3D Model Xchange](#)

[C25BNB AutoCAD 2D Footprint](#)

[C25BNB 2D PDF](#)

[C25BNB 2D Drawing Xchange](#)

[C25BNB AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25BNB230H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C25BNB230H

Catalog Number: C25BNB230H

Eaton definite purpose contactor, Quick, 30A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing



General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25BNB230H
UPC	Product Length/Depth
786685116051	2.32 in
Product Height	Product Width
3.19 in	1.97 in
Product Weight	Warranty
0.7 lb	1 year
Compliances	Certifications
RoHS Compliant	UL Recognized CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Two-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

Compact, two-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Binding head screw and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25BNB 3D Inventor](#)

[C25BNB 3D Model Xchange](#)

[C25BNB AutoCAD 2D Footprint](#)

[C25BNB 2D PDF](#)

[C25BNB 2D Drawing Xchange](#)

[C25BNB AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25BNB230H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)