

Eaton C25BNB230H

Catalog Number: C25BNB230H

Eaton definite purpose contactor, Quick, 30A, 440-480 Vac, 50/60 Hz, Open with metal mounting plate, Compact, two-pole, 30A, Contactor, Two-pole, 40A, Binding head screw and quick connect terminals (side-by-side), Non-reversing

Photo is representative



General specifications

| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25BNB230H |
| UPC | Product Length/Depth |
| 786685116051 | 2.32 in |
| Product Height | Product Width |
| 3.19 in | 1.97 in |
| Product Weight | Warranty |
| 0.7 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Two-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

Compact, two-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Terminals

Binding head screw and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25BNB AutoCAD 2D Footprint \(mm\)](#)

[C25BNB AutoCAD 2D Footprint](#)

[C25BNB 3D Inventor](#)

[C25BNB 3D Model Xchange](#)

[C25BNB 2D Drawing Xchange](#)

[C25BNB 2D PDF](#)

Specifications and datasheets

[Quick Selector - Definite Purpose Contactors](#)

[Eaton Specification Sheet - C25BNB230H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)