



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25BNB240T Compact 2P 40A Cont SCR Term Quad QC 24VAC Coil

Eaton Corp

Catalog Number	C25BNB240T
Manufacturer	Eaton Corp
Description	Eaton Definite Purpose Contactor, Quick, 40A, 277 Vac, 60 HZ, Open With Metal Mounting Plate, Compact, Two-Pole, 40A, Contactor, Two-Pole, 50A, Binding Head Screw and Quick Connect Terminals (Side-By-Side), Non-Reversing
Weight per unit	0.6000 (lbs/each)
Product Category	Definite Purpose Contactors

Features

connection	Quick
dimensions	2.3200 IN X 1.9700 IN X 3.1900 IN
Enclosure Type	Open with metal mounting plate

Dimensions and Weight

Depth	2.32
Height	3.19
Width	1.97

Descriptions

Description	COMPACT 2P 40A CONT SCR TERM QUAD QC 24VAC COIL
extra long description	ETN C25BNB240T COMPCT 2P 40A CONT S
Features	Definite purpose contactors and starters are electrically operated switching devices specifically designed for the heating, ventilation, air conditioning and refrigeration (HVAC) industry.
Long Description	Eaton definite purpose contactor, Quick, 40A, 277 Vac, 60 Hz, Open with metal mounting plate, Compact, two-pole, 40A, Contactor, Two-pole, 50A, Binding head screw and quick connect terminals (side-by-side), Non-reversing
Product Type	Compct 2P 40A Cont SCR Term 4QC 24vcoil

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685116105
Manufacturers Part Number	C25BNB240T
UPC	786685116105

Taxonomies, Classifications, and Categories

Category Description	DP CONTACTORS
Type	Definite purpose contactor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL Recognized, CSA Certified, RoHS Compliant