

Eaton C25DND330H

Catalog Number: C25DND330H

Eaton definite purpose contactor, Quick, 30A, 277 Vac, 60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 30A, Contactor, Three-pole, 40A, Screw/pressure plate and quick connect terminals (side-by-side), Non-reversing

General specifications



| | |
|----------------------------------|--------------------------------|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DND330H |
| UPC | Product Length/Depth |
| 782116308897 | 3.35 in |
| Product Height | Product Width |
| 2.5 in | 2.4 in |
| Product Weight | Warranty |
| 1.05 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified |

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25DND3 3D Model Xchange](#)

[C25DND3 2D Drawing Xchange](#)

[C25DND3 AutoCAD 2D Footprint \(mm\)](#)

[C25DND3 AutoCAD 2D Footprint](#)

[C25DND3 2D PDF](#)

[C25DND3 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C25DND330H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)