

Eaton C25DNF325T

Catalog Number: C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing



Photo is representative

General specifications

| | |
|----------------------------------|---|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DNF325T |
| UPC | Product Length/Depth |
| 782116300570 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 2.4 in |
| Product Weight | Warranty |
| 1.19 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2) |

Product specifications

Amperage Rating

25A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (side-by-side)

Coil

24 Vac, 50/60 Hz

Coil voltage

120 Vdc

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

35 A

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Specifications and datasheets

Eaton Specification Sheet - C25DNF325T



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton C25DNF325T

Catalog Number: C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing



Photo is representative

General specifications

| | |
|----------------------------------|---|
| Product Name | Catalog Number |
| Eaton definite purpose contactor | C25DNF325T |
| UPC | Product Length/Depth |
| 782116300570 | 3.35 in |
| Product Height | Product Width |
| 3.75 in | 2.4 in |
| Product Weight | Warranty |
| 1.19 lb | 1 year |
| Compliances | Certifications |
| RoHS Compliant | UL Recognized |
| | CSA Certified |
| | UL Listed file E1491 (Guide Number NLDX2) |

Product specifications

Amperage Rating

25A

Number Of Poles

Three-pole

Options

Global listed

Type

Non-reversing

Auxiliary contacts

Quick connect (side-by-side)

Coil

24 Vac, 50/60 Hz

Coil voltage

120 Vdc

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactor

Resistive load

35 A

Series

D1

Terminals

Box lugs (posidrive setscrew)

Connection

Quick

Resources

Specifications and datasheets

Eaton Specification Sheet - C25DNF325T



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)