

# Specifications



Photo is representative



## Eaton C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

<b>PRODUCT NAME</b>	Eaton definite purpose contactor
<b>CATALOG NUMBER</b>	C25DNF325T
<b>UPC</b>	782116300570
<b>PRODUCT LENGTH/DEPTH</b>	3.35 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	2.4 in
<b>PRODUCT WEIGHT</b>	1.19 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	25A
NUMBER OF POLES	Three-pole
OPTIONS	Global listed
TYPE	Non-reversing
AUXILIARY CONTACTS	Quick connect (side-by-side)
COIL	24 Vac, 50/60 Hz
COIL VOLTAGE	120 Vdc
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactactor
RESISTIVE LOAD	35 A
SERIES	D1
TERMINALS	Box lugs (posidrive setscrew)
CONNECTION	Quick

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - C25DNF325T](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

### General specifications

<b>PRODUCT NAME</b>	Eaton definite purpose contactor
<b>CATALOG NUMBER</b>	C25DNF325T
<b>UPC</b>	782116300570
<b>PRODUCT LENGTH/DEPTH</b>	3.35 in
<b>PRODUCT HEIGHT</b>	3.75 in
<b>PRODUCT WIDTH</b>	2.4 in
<b>PRODUCT WEIGHT</b>	1.19 lb
<b>WARRANTY</b>	1 year
<b>COMPLIANCES</b>	RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)



Powering Business Worldwide

## Product specifications

<b>AMPERAGE RATING</b>	25A
<b>NUMBER OF POLES</b>	Three-pole
<b>OPTIONS</b>	Global listed
<b>TYPE</b>	Non-reversing
<b>AUXILIARY CONTACTS</b>	Quick connect (side-by-side)
<b>COIL</b>	24 Vac, 50/60 Hz
<b>COIL VOLTAGE</b>	120 Vdc
<b>ENCLOSURE</b>	Open with metal mounting plate
<b>FRAME SIZE</b>	15-50 A, two-pole and three-pole
<b>INDUCTIVE FULL LOAD</b>	30 A
<b>MODEL</b>	Contactactor
<b>RESISTIVE LOAD</b>	35 A
<b>SERIES</b>	D1
<b>TERMINALS</b>	Box lugs (posidrive setscrew)
<b>CONNECTION</b>	Quick

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - C25DNF325T](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

