

Specifications

Photo is representative

Eaton C25DNF325T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect , 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and 3P, 25A, Contactor, 3P, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF325T
UPC	782116300570
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.19 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)
PRODUCT TYPE	Definite purpose contactor



Powering Business Worldwide

Product specifications

AMPERAGE RATING	25A
NUMBER OF POLES	Three-pole
OPTIONS	Global listed
TYPE	Non-reversing
AUXILIARY CONTACTS	Quick connect (side-by-side)
COIL	24 Vac, 50/60 Hz
COIL VOLTAGE	120 Vdc
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactator
RESISTIVE LOAD	35 A
SERIES	D1
TERMINALS	Box lugs (posidrive setscrew)
CONNECTION	Quick

Resources

CATALOGS	Motor Control and Protection, Definite Purpose Contactors and Starters, Volume 5, Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C25DNF325T

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

