

Specifications

Photo is representative

Eaton C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF330T
UPC	782116311422
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.19 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized UL Listed



Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
TYPE	Non-reversing
AUXILIARY CONTACTS	Pressure plate and quick connect
COIL	24 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C25DNF330T](#)

MODEL	Contactor
RESISTIVE LOAD	40 A
TERMINALS	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
CONNECTION	Quick

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF330T
UPC	782116311422
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.19 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized UL Listed



Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
TYPE	Non-reversing
AUXILIARY CONTACTS	Pressure plate and quick connect
COIL	24 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - C25DNF330T](#)

MODEL	Contactor
RESISTIVE LOAD	40 A
TERMINALS	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
CONNECTION	Quick

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

