

Eaton C25END430A

Catalog Number: C25END430A

Eaton Definite purpose control contactor, Non-reversing, Four-pole, 30A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, Screw/pressure plate and quick connect terminals (side-by-side), 30A IFL, 40A RL

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25END430A
UPC	Product Length/Depth
782113542331	3.38 in
Product Height	Product Width
3.75 in	2.68 in
Product Weight	Warranty
2.3 lb	1 year
Certifications	Catalog Notes
CSA Certified UL Recognized	Resistive Load rating per pole

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Four-pole

Type

Non-reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

25-40 A, four-pole

Inductive full load

30 A

Model

Contactor

Resistive load

40 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25END4 3D Inventor](#)

[C25END4 2D Drawing Xchange](#)

[C25END4 AutoCAD 2D Footprint](#)

[C25END4 3D Model Xchange](#)

[C25END4 AutoCAD 2D Footprint \(mm\)](#)

[C25END4 2D PDF](#)

Specifications and datasheets

[Eaton Specification Sheet - C25END430A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)