

Eaton C25FNF350B

Catalog Number: C25FNF350B

Eaton definite purpose contactor, Quick, 50A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 50A, Contactor, Three-pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25FNF350B
UPC	Product Length/Depth
782113476087	3.97 in
Product Height	Product Width
3.75 in	2.63 in
Product Weight	Warranty
2.7 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized
Catalog Notes	
Resistive Load rating per pole	

defaultTaxonomyAttributeLabel

Amperage Rating

50A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

208-240 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

50 A

Model

Contactors

Resistive load

65 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C25FNF350B](#)