

Eaton C25FNF360B

Catalog Number: C25FNF360B

Eaton definite purpose contactor, Quick, 60A, 208-240 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 60A, Contactor, Three-pole, 75A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25FNF360B

UPC

782113476148

Product Length/Depth

3.97 in

Product Height

3.75 in

Product Width

2.63 in

Product Weight

2.65 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

CSA Certified
UL Recognized

Catalog Notes

Resistive Load rating per pole

defaultTaxonomyAttributeLabel

Amperage Rating

60A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

208-240 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

60 A

Model

Contactors

Resistive load

75 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25FNF3 2D PDF](#)

[C25FNF3 AutoCAD 2D Footprint](#)

[C25FNF3 3D Model Xchange](#)

[C25FNF3 AutoCAD 2D Footprint \(mm\)](#)

[C25FNF3 3D Inventor](#)

Specifications and datasheets

[Eaton Specification Sheet - C25FNF360B](#)