

Eaton C25FNF360T

Catalog Number: C25FNF360T

DC DP CONTACTOR 30 AMP, Quick,Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing

General specifications



Photo is representative

Product Name	Catalog Number
Eaton definite purpose contactor	C25FNF360T
UPC	Product Length/Depth
782113476155	3.97 in
Product Height	Product Width
3.75 in	2.63 in
Product Weight	Warranty
2.65 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified
	UL Recognized

Catalog Notes

Resistive Load rating per pole

Amperage Rating

75A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

110-120 Vac, 50/60 Hz

Contact configuration

1 NO, 1 NC

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

75 A

Model

Contactor

Resistive load

90 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Catalogs[Eaton's Volume 5—Motor Control and Protection](#)**Drawings**[C25FNF3 3D Model Xchange](#)[C25FNF3 2D PDF](#)[C25FNF3 AutoCAD 2D Footprint](#)[C25FNF3 AutoCAD 2D Footprint \(mm\)](#)[C25FNF3 3D Inventor](#)**Specifications and datasheets**[Eaton Specification Sheet - C25FNF360T](#)