



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Freedom Thermal Overload Relay

**C306GN3B**

UPC:782113973241

### Dimensions:

- Height: X
- Length: X
- Width: X

**Notes:** Series B overload relays have load lugs built into relay base and will only accept Series B heater packs. These relays can be directly attached to a contactor or they can be DIN rail or panel mounted using an adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 60-79A
- **Design:** NEMA, IEC
- **Frame Size:** NEMA Size 1, 2, IEC Size G-K
- **Mounting:** Panel
- **Number Of Poles:** Three-pole
- **Special Features:** Heaters required
- **Trip Type:** Thermal

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Motor Starters and Contactors - Low Voltage Catalog](#)
- [C306GN3B 2D Drawing Xchange](#)
- [C306GN3B AutoCAD 2D Footprint \(mm\)](#)
- [C306GN3B 2D PDF](#)
- [C306GN3B AutoCAD 2D Footprint](#)
- [C306GN3B 3D Inventor](#)



- [C306GN3B 3D Model Xchange](#)
- [Eaton Specification Sheet - C306GN3B](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NEMA Freedom Thermal Overload Relay

**C306GN3B**

**UPC:**782113973241

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:** Series B overload relays have load lugs built into relay base and will only accept Series B heater packs. These relays can be directly attached to a contactor or they can be DIN rail or panel mounted using an adapter.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 60-79A
- **Design:** NEMA, IEC
- **Frame Size:** NEMA Size 1, 2, IEC Size G-K
- **Mounting:** Panel
- **Number Of Poles:** Three-pole
- **Special Features:** Heaters required
- **Trip Type:** Thermal

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Motor Starters and Contactors - Low Voltage Catalog](#)
- [C306GN3B 2D Drawing Xchange](#)
- [C306GN3B AutoCAD 2D Footprint \(mm\)](#)
- [C306GN3B 2D PDF](#)
- [C306GN3B AutoCAD 2D Footprint](#)
- [C306GN3B 3D Inventor](#)



- [C306GN3B 3D Model Xchange](#)
- [Eaton Specification Sheet - C306GN3B](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.