



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C515M 15 Min Twist Timer With Metal Wallplate

Nsi Industries

Catalog Number	C515M
Manufacturer	Nsi Industries
Description	The Tork C515M 15-Minute Spring-Wound In-Wall Twist Timer With A Commercial-Style Metal Faceplate Is Designed to Control A Variety Of Indoor Appliances, Motors and Lights. Automate Factories, Offices or Other Buildings to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For SPDT Switch Type On Indoor Loads Such As Ventilation Fans, Lighting, Hvac Systems, Motors, Pumps or Air Compressors.
Weight per unit	0.4000 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	15 Minute



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	15 MIN TWIST TIMER WITH METAL WALLPLATE
extra long description	TORK C515M CU CMP Splice Long 6 AWG
Features	The TORK C515M spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applicat
Long Description	The TORK C515M 15-Minute Spring-Wound In-Wall Twist Timer with a commercial-style metal faceplate is designed to control a variety of indoor appliances, motors and lights. Automate factories, offices or other buildings to save energy and money using the simple twist knob and reliable mechanical timekeeping. Fits into a standard electrical box for in-wall mounting. Designed for SPDT switch type on indoor loads such as ventilation fans, lighting, HVAC systems, motors, pumps or air compressors.
Product Type	Cu CMP Splice Long 6 Awg

Manufacturer Information

Brand	NSi
GTIN	00786261155016
Manufacturers Part Number	C515M
sub brand	In Wall Timers
UPC	786261155016

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
----------------------	-------------

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F