ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1774 Buildtek Court
88005-0000, NM Las Cruces
Phone: 575-652-6525
Fax: 000-000-0000



C515M 15 Min Twist Timer With Metal Wallplate

Nsi Industries

Catalog Number	C515M
Manufacturer	Nsi Industries
Description	The Tork C515M 15-Minute Spring-Wound In-Wall Twist Timer With A Commercial-Style Metal Faceplate Is Designed to Control A Variety Of Indoor Appliances, Motors and Lights. Automate Factories, Offices or Other Buildings to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For SPDT Switch Type On Indoor Loads Such As Ventilation Fans, Lighting, Hvac Systems, Motors, Pumps or Air Compressors.
Weight per unit	0.4000 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Timing Range	15 Minute

Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

1774 Buildtek Court
88005-0000, NM Las Cruces
Phone: 575-652-6525
Fax: 000-000-0000

Descriptions

Description	15 MIN TWIST TIMER WITH METAL WALLPLATE
extra long description	TORK C515M 15 Minute Spring Wound T
Features	The TORK C515M spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applicat
Long Description	The TORK C515M 15-Minute Spring-Wound In-Wall Twist Timer with a commercial-style metal faceplate is designed to control a variety of indoor appliances, motors and lights. Automate factories, offices or other buildings to save energy and money using the simple twist knob and reliable mechanical timekeeping. Fits into a standard electrical box for in-wall mounting. Designed for SPDT switch type on indoor loads such as ventilation fans, lighting, HVAC systems, motors, pumps or air compressors.
Product Type	15 Minute Spring Wound Twist Timer 125-277V SPDT Metal Wallp

Manufacturer Information

Brand	Nsi Industries
GTIN	00786261155016
Manufacturers Part Number	C515M
UPC	786261155016

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Frequency Rating	50-60 Hz
Operating Temperature	32-122 F