

NEER Zinc Two Screw Connectors

For Service Entrance Cable

COMMERCIAL PRODUCTS: SERVICE ENTRANCE FITTINGS

Commercial Products

C: For Oval Service Entrance Cables

Applications

- To terminate oval Type SE or Type USE cable.

Features

- Furnished with locknut.
- Male hub threads — NPS.

Standard Material/Finish

- Body: zinc diecast
- Clamp (C-750, C-1001-R): steel/zinc plated
- Clamp (C-1250, C-1500, C-2000): zinc diecast
- Screw: steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E25015
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1

Note:

- C-750 and C-1001-R also listed for use with nonmetallic sheathed cable.



C-750 and C-1001-R

C-1250 thru C-2000

C-R: For Round Service Entrance Cables

Application

- To terminate round Type SE or Type USE cable to a knockout in dry location box or enclosure.

Features


- Furnished with locknut.
- Male hub threads — NPS.

Standard Material/Finish

- Body: zinc diecast
- Clamp: steel/zinc plated
- Screw: steel/zinc plated

Certifications and Compliances

- UL Standard: 514B
- UL Listed: E25015
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 208044
- NEMA: FB-1



C-1001-R thru
C-1501-R

C-2001-R

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			Range
		A	B	C	
3/4	C-750	0.42/ 10.7	0.94/ 23.9	0.91/ 23.1	8-3, 6-3 SE
1	C-1001-R	0.51/ 13.0	1.11/ 28.2	1.20/ 30.5	10-3, 4-2 SE
1-1/4	C-1250	0.60/ 15.2	1.31/ 33.3	1.87/ 47.5	3-3, 2-3 SE
1-1/2	C-1500	0.59/ 15.0	1.33/ 33.8	2.01/ 51.1	3-2/0 SE
2	C-2000	0.74/ 18.8	1.57/ 39.9	2.62/ 66.5	3-4/0 SE

Trade Size (Inches)	Catalog Number	Dimensions in Inches/Millimeters			Range
		A	B	C	
1	C-1001-R	0.51/ 13.0	1.11/ 28.2	1.51/ 38.4	6-3, 4-3 SER
1-1/4	C-1251-R	0.60/ 15.2	1.25/ 31.8	1.82/ 46.2	3-3, 2-3 SER
1-1/2	C-1501-R	0.64/ 16.3	1.44/ 36.6	2.06/ 52.3	3-2/0, 3-3/0 SER
2	C-2001-R *	0.74/ 18.8	1.59/ 40.4	2.58/ 65.5	4-4/0 SER

* Not UL Listed or CSA Certified.