



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C8N 8AWG Closed End Wire Nyl Conn W/CRMP SLV

Nsi Industries

| | |
|------------------|--|
| Catalog Number | C8N |
| Manufacturer | Nsi Industries |
| Description | The Easy-Twist C8-N 40-Count Pack Of Nylon Closed-End Wire Connectors Are Designed For Use On Pre-Insulated Wires In The 16-10 Awg Size Range. Theyâ€™re UI-Certified As Self-Extinguishing and Rated For A Maximum Temperature Of 105Ëš Celsius (221Ëš Fahrenheit). The Closed-End Nylon Connector Features An Internal Metal Crimp Sleeve That Can Be Tightened Over Twisted Pre-Insulated Wires to Form A Safe and Secure Join. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to |
| Weight per unit | N/A |
| Product Category | Tools & Testers |

Features

| | |
|----------------------|--------------|
| insulation | Nylon 66 |
| Material | Nylon |
| Number of Conductors | 1 |
| Poles | 1 |
| Voltage Rating | 300 V |
| Warranty | 1 YEAR |
| Wire Size | 16-10 AWG |
| Wire Type | CU Wire Only |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | NYLON |

Dimensions and Weight

| | |
|------|--------------------------|
| Size | H=1.09 - W=.563 -ID=.209 |
|------|--------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 8AWG CLOSED END WIRE NYL CONN W/CRMP SLV |
| extra long description | NSI C8-N Easy Twist Closed End Conn |
| Features | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These closed-end connectors feature a corrosion and chemical resistant nylon cover over a metal crimp cap wire terminal. These connectors are easy to install; simply twist your wires together to form a connection, then slide the closed end butt connector over the pigtail and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these closed-end conn |
| Long Description | The Easy-Twist C8-N 40-Count Pack of Nylon Closed-End Wire Connectors are designed for use on pre-insulated wires in the 16-10 AWG size range. They are UL-certified as self-extinguishing and rated for a maximum temperature of 105°C (221°F). The closed-end nylon connector features an internal metal crimp sleeve that can be tightened over twisted pre-insulated wires to form a safe and secure join. Their compact design is useful for applications in tight areas or anywhere else you need to |
| Product Type | Easy Twist Closed End Conn 16-10 40 PK |
| Special Features | 16-10 AWG - UL94 V-2 - Made From Nylon 66 - 40 Pcs Blister |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSI |
| GTIN | 00662381362094 |
| Manufacturers Part Number | C8-N |
| UPC | 662381362094 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------|
| Category Description | TERMINALS |
| Type | Closed End Connectors |

Availability

| | |
|-------------|----|
| minimum qty | 30 |
|-------------|----|

Packaging

| | |
|-----------------|----|
| Carton | 30 |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|--------------------------|---------------|
| Application | Splicing Wire |
| environmental conditions | 105 C |
| standard | UL 486C |
| Temperature Rating | 105 C |