

# Eaton CCP3033BC

Catalog Number: CCP3033BC

Eaton Crouse-Hinds series PowerMate CCP plug, 30A, 0.390-1.375", Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CCP plug	CCP3033BC
	UPC
	662276276529
Product Length/Depth	Product Height
6.5 in	2.31 in
Product Width	Product Weight
2.31 in	2.2 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

30A

### Grounding type

Style 1

### Configuration

Three-wire, three-pole

### Cable diameter

0.390-1.375"

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds CCP3033BC 3D drawing](#)

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

### Installation instructions

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

### Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP3033BC](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)