

Eaton CCV2100

Catalog Number: CCV2100

Eaton Type CCV Tenant Main Circuit Breaker, Tenant main circuit breaker, 100 A, 10 kAIC, Two-pole, 120/240 V, #2/0 AWG-300 kcmil Cu/Al, CCV, Type ECC unit enclosures

General specifications



Product Name

Eaton CCV tenant main breaker

Catalog Number

CCV2100

UPC

786685368337

Product Length/Depth

7.7 in

Product Height

5.4 in

Product Width

4.5 in

Product Weight

3 lb

Warranty

Limited lifetime residential, 1 year commercial

Certifications

UL 489

Catalog Notes

Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

Type

Tenant main circuit breaker

Amperage Rating

100 A

Voltage rating

120/240 V

Circuit breaker frame type

CCV

Used with

Type ECC Unit Enclosures

Interrupt rating

10 kAIC

Main circuit breaker

CCV

Wire size

#2/0 AWG-300 kcmil Cu/Al

Number of poles

Two-pole

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CCV2100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)