

# Eaton CE15CNS3AB

Catalog Number: CE15CNS3AB

Eaton XT IEC contactor, 12A, 110-120 Vac, 50-60 Hz, 1NO, 12A, Frame C, 45 mm, 50-60 Hz, 0.5 hp, Side, Three-pole, Non-reversing, No overload relay, Freedom, Contactor



## General specifications

### Product Name

Eaton XT IEC contactor

### Catalog Number

CE15CNS3AB

### UPC

782113778457

### Product Length/Depth

3.25 in

### Product Height

2.96 in

### Product Width

1.8 in

### Product Weight

0.9 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

DIN VDE 0600  
ISO 9000

### Certifications

IEC Rated  
CSA Certified  
UL Listed

### Catalog Notes

Fourth power pole position is used as the auxiliary contact and adds no additional width. No enclosure.

## defaultTaxonomyAttributeLabel

### Amperage Rating

12A

### HP rating - max

0.5 hp

### Number Of Poles

Three-pole

### Type

Contactora

### Frequency rating

50-60 Hz

### Frame size

45 mm

### Coil voltage

110-120 Vac, 50-60 Hz

### Contact configuration

1 NO

### Continuous ampere rating

12 A

### Relay

No overload relay

### Series

Freedom

### Operation

Non-reversing

### Mounting method

Side

## Resources

### Catalogs

[Motor Starters and Contactors — Low Voltage Catalog](#)

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - CE15CNS3AB](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)