ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188



CF26DTEIN835 26W 4 Pin Triple Tube Biax GX24Q-3 3500K Compact

Sylvania-Ledvance

Catalog Number	CF26DTEIN835
Manufacturer	Sylvania-Ledvance
Description	Dulux 26W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 3500K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2300 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24q-3
Lamp Type	DULUX T/E
lumens	1,746
Shape	T4
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	26

Material, Color, and Finish

color rendering index (cri)	82
color temperature	3500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	0.500000000000000
Length	5

Descriptions

Description	26W 4 PIN TRIPLE TUBE BIAX GX24Q-3 3500K COMPACT
extra long description	LDV CF26DT/E/IN/835/ECO/20881 CF26D
Long Description	DULUX 26W triple compact fluorescent amalgam lamp with 4 pin base, 3500K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF26DTEIN835ECO 50/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135208812
Manufacturers Part Number	CF26DT/E/IN/835/ECO/20881
UPC	046135208812

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
537 N 40th St
72762-0000, AR Springdale
Phone: 479-361-2266
Fax: 479-361-9188

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent

Availability

Status	Inactive

Packaging

Carton	1
Package	50
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Commercial/Residential