



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CGB195 1/2" Dia Male Cord Grip (.500-.625)

Crouse-Hinds

Catalog Number	CGB195
Manufacturer	Crouse-Hinds
Description	Cord Gland, Steel With Zinc Electroplate and Chromate Finish Coat (Body, Gland Nut); Neoprene (Bushing) Material, CGB Model, 0.5 to 0.625 In Cable/Cord Size, 2.063 In Length, 1.23 In Diameter, Straight Male Connection, 1/2 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 0.18 LB
Weight per unit	0.1800 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	2.0200 IN X 1.2300 IN X 1.2300 IN

Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	1/2" DIA MALE CORD GRIP (.500-.625)
extra long description	CRS-H CGB195 1/2 NPT MALE CORD/CAB
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

Manufacturer Information

Brand	Eaton
GTIN	00782274131306
UPC	782274131306

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Weight Per each	0.18

Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C