

Specifications



Eaton CH12L200R

Eaton CH main lug loadcenters, Cover included, Main lug only, 200A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton CH main lug loadcenter |
| CATALOG NUMBER | CH12L200R |
| UPC | 782113097404 |
| PRODUCT LENGTH/DEPTH | 29.13 in |
| PRODUCT HEIGHT | 5.19 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 29.8 lb |
| WARRANTY | Limited lifetime |
| CERTIFICATIONS | UL 50 UL 67 |
| CATALOG NOTES | Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb. |



Powering Business Worldwide

Product specifications

| | |
|-------------------------|----------------|
| SPECIAL FEATURES | Cover included |
| TYPE | Main lug only |
| AMPERAGE RATING | 200 A |
| BUS MATERIAL | Copper |

Resources

| | |
|-------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| MULTIMEDIA | AFCI Educational Video |

| | |
|-----------------------------|------------------|
| FEED TYPE | Overhead |
| MAIN CIRCUIT BREAKER | CH |
| NUMBER OF CIRCUITS | 12 |
| NUMBER OF SPACES | 12 |
| PHASE | Single-phase |
| VOLTAGE RATING | 120/240 V |
| WIRE SIZE | #4 AWG-300 kcmil |
| BOX SIZE | D |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| NUMBER OF WIRES | 3 |

| | |
|--------------------------------------|--|
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - CH12L200R |
| WARRANTY GUIDES | Eaton type CH circuit breaker limited warranty June 2024 |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton CH12L200R

Eaton CH main lug loadcenters, Cover included, Main lug only, 200A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 12, 12, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton CH main lug loadcenter |
| CATALOG NUMBER | CH12L200R |
| UPC | 782113097404 |
| PRODUCT LENGTH/DEPTH | 29.13 in |
| PRODUCT HEIGHT | 5.19 in |
| PRODUCT WIDTH | 14.31 in |
| PRODUCT WEIGHT | 29.8 lb |
| WARRANTY | Limited lifetime |
| CERTIFICATIONS | UL 50 UL 67 |
| CATALOG NOTES | Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb. |



Powering Business Worldwide

Product specifications

| | |
|-------------------------|----------------|
| SPECIAL FEATURES | Cover included |
| TYPE | Main lug only |
| AMPERAGE RATING | 200 A |
| BUS MATERIAL | Copper |

Resources

| | |
|-------------------|--|
| CATALOGS | Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1 |
| MULTIMEDIA | AFCI Educational Video |

| | |
|-----------------------------|------------------|
| FEED TYPE | Overhead |
| MAIN CIRCUIT BREAKER | CH |
| NUMBER OF CIRCUITS | 12 |
| NUMBER OF SPACES | 12 |
| PHASE | Single-phase |
| VOLTAGE RATING | 120/240 V |
| WIRE SIZE | #4 AWG-300 kcmil |
| BOX SIZE | D |
| ENCLOSURE | NEMA 3R |
| ENCLOSURE MATERIAL | Metallic |
| NUMBER OF WIRES | 3 |

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - CH12L200R](#)

WARRANTY GUIDES

[Eaton type CH circuit breaker limited warranty June 2024](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

