

Eaton CH20L125C

Catalog Number: CH20L125C

Eaton CH 3/4-inch loadcenter, single-phase, 20 circuits, 20-pole, #6-2/0 wire, 125Amp, NEMA 1



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH20L125C
UPC	Product Length/Depth
782113097572	29.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.

Product specifications

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Cover

Ch8cf-combination, ch8cs-surface

Feed type

Top/bottom

Main circuit breaker

CH

Number of circuits

20

Number of spaces

20

Phase

Single-phase

Wire size

#6-2/0 AWG

Box size

C

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH20L125C](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)