

Eaton CH2125

Catalog Number: CH2125

Eaton CH Thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 125 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters

General specifications



Product Name

Eaton CH thermal magnetic circuit breaker

Catalog Number

CH2125

UPC

782113298788

Product Length/Depth

3.75 in

Product Height

2.75 in

Product Width

2.5 in

Product Weight

0.58 lb

Certifications

UL 489

Catalog Notes

Two-Pole 120/240V Common Trip
Requires Two 3/4-Inch Spaces



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Amperage Rating

125 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#10-1/0 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH2125](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)