



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH22N125C

UPC:782113098494

Dimensions:

- **Height:** 3.88 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes: Panel does not include main. Order main breaker/lug kit separately. Loadcenters are factory bonded for service entrance apps. Remove bonding strap for separate neutral & ground bars for sub-feed apps.

Warranties:

- Limited lifetime

Specifications:

- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Cover:** Ch8cf-combination, ch8cs-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 22
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #10-1/0 AWG

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH22N125C](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH22N125C

UPC:782113098494

Dimensions:

- **Height:** 3.88 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes: Panel does not include main. Order main breaker/lug kit separately. Loadcenters are factory bonded for service entrance apps. Remove bonding strap for separate neutral & ground bars for sub-feed apps.

Warranties:

- Limited lifetime

Specifications:

- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Cover:** Ch8cf-combination, ch8cs-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 22
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #10-1/0 AWG

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH22N125C](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.