

Eaton CH22N125R

Catalog Number: CH22N125R

CH 3/4-inch loadcenter, single-phase, 22 circuits, 22-pole, #10-1/0 wire, 125A, NEMA 3R



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CH22N125R
UPC	Product Length/Depth
782113098524	22.1 in
Product Height	Product Width
5.1 in	15.6 in
Product Weight	Warranty
25 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Furnished with hub closure plates.
UL 50	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Convertible loadcenter

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

22

Number of spaces

22

Phase

Single-phase

Wire size

#10-1/0 AWG

Box size

C

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH22N125R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)