

Specifications



Eaton CH24B150R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 150 A, E, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V

General specifications

PRODUCT NAME	Eaton CH main breaker loadcenter
CATALOG NUMBER	CH24B150R
UPC	782113097763
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	32.85 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Cover included
TYPE	Main breaker
AMPERAGE RATING	150 A
BUS MATERIAL	Copper

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video

MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	24
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil
FEED TYPE	Overhead
VOLTAGE RATING	120/240 V
BOX SIZE	E
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH24B150R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications



Eaton CH24B150R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 150 A, E, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V

General specifications

PRODUCT NAME	Eaton CH main breaker loadcenter
CATALOG NUMBER	CH24B150R
UPC	782113097763
PRODUCT LENGTH/DEPTH	29.13 in
PRODUCT HEIGHT	5.19 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	32.85 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 67 UL 50
CATALOG NOTES	Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.



Product specifications

SPECIAL FEATURES	Cover included
TYPE	Main breaker
AMPERAGE RATING	150 A
BUS MATERIAL	Copper

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video

MAIN CIRCUIT BREAKER	CSR
NUMBER OF CIRCUITS	24
NUMBER OF SPACES	24
PHASE	Single-phase
WIRE SIZE	#2/0 AWG-300 kcmil
FEED TYPE	Overhead
VOLTAGE RATING	120/240 V
BOX SIZE	E
ENCLOSURE	NEMA 3R
ENCLOSURE MATERIAL	Metallic
INTERRUPT RATING	25 kAIC
NUMBER OF WIRES	3

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH24B150R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

