



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352



CH24BPN100E 24C 100A 1PH MB Plug-On Neutral Loadcenter

Eaton Corp

| | |
|------------------|---|
| Catalog Number | CH24BPN100E |
| Manufacturer | Eaton Corp |
| Description | CH 3/4-Inch Loadcenter, Single-Phase, 24 Circuits, 24-Pole, #2/0-300 Kcmil Wire, 100A, Nema 1 |
| Weight per unit | 32.0 (lbs/each) |
| Product Category | Single Phase Main Breaker Load |

Features

| | |
|----------------------|---|
| amperage rating | 100 WTT |
| Box Size | E |
| cover | Ch8ef-combination, ch8es-surface, not included |
| Cover Type | Ch8ef-combination, ch8es-surface, not included |
| dimensions | 73.9902centimetreX36.3474centimetreX98.5520millimetre |
| interrupt rating | 25 kAIC |
| main circuit breaker | CSH |
| max amps | 100 |
| max poles | 24 |
| Number of Circuits | 24 VDC |
| number of spaces | 24 VDC |
| Number of Wires | Three-wire |
| Phase | 1 PH |
| Poles | 24-pole |
| Wire Size | #2/0-300 kcmil |

Material, Color, and Finish

| | |
|--------------------|----------|
| Bus Material | Copper |
| Enclosure Material | Metallic |

Dimensions and Weight

| | |
|------|---|
| Size | E |
|------|---|

Descriptions

| | |
|------------------------|---|
| Description | 24C 100A 1PH MB PLUG-ON NEUTRAL LOADCENTER |
| extra long description | ETN CH24BPN100E CH 3/4-inch loadcen |
| Long Description | CH 3/4-inch loadcenter, single-phase, 24 circuits, 24-pole, #2/0-300 kcmil wire, 100A, NEMA 1 |
| Product Type | CH 3/4-Inch Loadcenter |
| Special Features | Plug-on neutral |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1220 Elm Street
75482-0000, TX Sulphur Springs
Phone: 903-885-0024
Fax: 903-885-0352

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN | 00782116983360 |
| Manufacturers Part Number | CH24BPN100E |
| UPC | 782116983360 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LOADCENTERS & COVERS |
| igcc | PLUG, NON POLARIZED TYPE; THERMOPLASTIC MATERIAL; WHITE COLOR; 1-15P CONFIGURATION; UL 1706, CSA APPROVAL; 125 V VOLTAGE RATING; 15 AMPERE CURRENT RATING; IMPACT RESISTANT; (2) 18 AWG CORD SIZE; HOMeselect[T] BRAND |
| Type | MAIN BREAKER |
| unspsc code | MODULAR LINE CORD, TELEPHONE LINE EXTENSION CORD TYPE; 15 FT LENGTH IN FT; METALLIC COLOR FAMILY; SILVER MANUFACTURERS COLOR NAME; GC[T] BRAND; CONNECTOR TYPE MODULAR PLUG; CORD SIZE (6) 26 AWG |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 32 |

Uses, Certifications, and Standards

| | |
|-----------|-------------|
| Enclosure | NEMA 1 |
| standard | UL 67,UL 50 |