

Eaton CH250GFT

Catalog Number: CH250GFT

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, 50 A, 10 kAIC, Two-pole, 120/240 V, CH, Common, Plug-on, #14-4 AWG, Ground fault self test, GFI



General specifications

| | |
|-------------------------------|--|
| Product Name | Catalog Number |
| Eaton CH GFCI circuit breaker | CH250GFT |
| UPC | Product Length/Depth |
| 786676025652 | 4.5 in |
| Product Height | Product Width |
| 2 in | 2.75 in |
| Product Weight | Warranty |
| 0.7 lb | 10 year |
| Certifications | Catalog Notes |
| UL 489 | Meets Federal Spec Classification W-C375 |

Type

Ground fault circuit breaker

Special features

Ground Fault Self Test

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault self test

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Plug-on

Wire size

#14-4 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - CH250GFT](#)