



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CH 3/4-inch loadcenter

CH30B125D

UPC:782113097831

### Dimensions:

- **Height:** 3.88 IN
- **Length:** 29.13 IN
- **Width:** 14.31 IN

**Notes:** Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

### Warranties:

- Limited lifetime

### Specifications:

- **Special Features:** Standard
- **Type:** Main breaker
- **Amperage Rating:** 125A
- **Box Size:** D
- **Bus Material:** Copper
- **Cover:** Ch8df-combination, ch8ds-surface, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 30
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #6-1/0
- **Feed Type:** Overhead or underground

### Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH30B125D](#)



- Dimensional Drawing - CH 3/4 LOADCENTER,  
CH MAIN BREAKER, INDOOR NEMA 1,  
120/240 VAC, 1 PHASE

**Certifications:**

- UL 67
- UL 50

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.