

# Eaton CH30L3150R

Catalog Number: CH30L3150R

Eaton CH main lug loadcenter, Standard, Main lug only, 150 A,D, Copper, NEMA 3R, Metallic, Overhead, CH, 30 Circuits, 30 Spaces, Four-wire, Three-phase, #4 AWG-300 kcmil



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CH30L3150R
<b>UPC</b>	<b>Product Length/Depth</b>
782113097916	29.13 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
34.8 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Furnished with hub closure plates.

## Product specifications

### Number of spaces

30

### Special features

Standard

### Interrupt rating

35 kAIC

### Phase

Three-phase

### Wire size

#4 AWG-300 kcmil

### Bus material

Copper

### Main circuit breaker

CH

### Enclosure

NEMA 3R

### Amperage Rating

150 A

### Enclosure material

Metallic

### Type

Main lug only

### Feed type

Overhead

### Number of wires

4

### Number of circuits

30

### Box size

D

## Resources

### Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PH

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH30L3150R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)