

Eaton CH32B200R

Catalog Number: CH32B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, J, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Overhead, 120/240 V



General specifications

Product Name

Eaton CH main breaker loadcenter

Catalog Number

CH32B200R

UPC

782113098135

Product Length/Depth

34.13 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

15.8 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22.

Loadcenter contains single insulated/bondable neutral.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Feed type

Overhead

Voltage rating

120/240 V

Box size

J

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH32B200R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)