

Eaton CH32B200V

Catalog Number: CH32B200V

CH 3/4-inch loadcenter, Standard, Main breaker, 200A, J, Copper, NEMA 1, Metallic, 25 kAIC, CSR, 32, 32, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Csh2125n, csh2200n, csh2100n



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH32B200V
UPC	Product Length/Depth
782114290262	34.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Value packs breakers included 5-ch120 & 1-ch230

Product specifications

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Main breaker kit

Csh2125n, csh2200n, csh2100n

Box size

J

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH32B200V](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)